

# PALBOT 2017

- powered by D:PLOY



## TECH SPECIFICATIONS

- **MAX CYCLE TIME\***  
10 box/min
- **FOOTPRINT**  
2.5 x 1.7 m
- **MAX BOX PAYLOAD\***  
15 kg
- **MAX PALLET HEIGHT\***  
1.8 m
- **FLEXIBLE PALLET SIZES**  
Yes
- **ROBOT MODEL**  
Doosan H2017
- **ROBOT MOUNTING**  
Fixed pedestal

\* Actual performance may differ depending on setup and other environmental factors

## SAFETY

- **SAFETY CERTIFICATION**  
CE is included
- **SAFETY CONFIGURATION**  
2 safety scanners included

## UNIQUE FEATURES

- **PALLET ARRANGEMENT**  
Dual side
- **BASE MATERIAL**  
Bent sheet metal
- **PALLET DETECTION**  
Two photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**  
Yes, tablet
- **LIGHT INDICATORS**  
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**  
Yes, manual pallet confirmation button
- **CONVEYOR\*\***  
Available as an option
- **INTERLAYER CONTAINER\*\***  
Available as an option

\*\* The inclusion of additional features may affect the final price