

# QP25

## - POWERED BY D:PLOY



## TECH SPECIFICATIONS

- **MAX CYCLE TIME\***  
3 box/min collaborative mode  
6 box/min high-speed mode
- **FOOTPRINT**  
3 m x 1.3 m
- **MAX BOX PAYLOAD\***  
20 kg
- **MAX PALLET HEIGHT\***  
1.9 m
- **FLEXIBLE PALLET SIZES**  
Yes
- **ROBOT MODEL**  
Fanuc CRX-30iA
- **ROBOT MOUNTING**  
Fixed pedestal

\* Actual performance may differ depending on setup and other environmental factors

## SAFETY

- **SAFETY CERTIFICATION**  
CE is included
- **SAFETY CONFIGURATION**  
Cobot mode (as an option, 3 safety scanners can be included to increase cycle time)

## UNIQUE FEATURES

- **PALLET ARRANGEMENT**  
Dual side
- **BASE MATERIAL**  
Alu. Profile
- **PALLET DETECTION**  
OnRobot pallet station
- **OPERATOR INTERFACE INCLUDED**  
Yes, robot tablet
- **LIGHT INDICATORS**  
Yes, application status indicator and pallet presence indicator
- **MANUAL CONTROL BUTTONS**  
Not included
- **CONVEYOR\*\***  
Available as an option
- **INTERLAYER CONTAINER**  
Not included

\*\* The inclusion of additional features may affect the final price