

RCP12-S-V

- powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
2.3 x 1.7 m
- **MAX BOX PAYLOAD**
9 kg
- **MAX PALLET HEIGHT***
Up to 1.3 m
- **FLEXIBLE PALLET SIZES**
Only EUR pallet or smaller
- **ROBOT MODEL**
JAKA Zu12
- **ROBOT MOUNTING**
Fixed pedestal

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
Yes (CE)
- **SAFETY CONFIGURATION**
3 safety scanners are included on the base solution (as an optional, a folding security fence + 1 safety scanner can be included on the base solution)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
2 sides
- **BASE MATERIAL**
Bent and weld sheet metal
- **PALLET DETECTION**
1 photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, an integrated touchscreen is included
- **LIGHT INDICATORS**
Yes, indicating the robot status
- **MANUAL CONTROL BUTTONS**
No
- **CONVEYOR****
No (available as an option)
- **INERLAYER CONTAINER****
No (available as an option)

** The inclusion of additional features may affect the final price