

AUTO COPAL 20

- powered by D:PLOY

TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
2 m x 2 m
- **MAX BOX PAYLOAD***
15 kg
- **MAX PALLET HEIGHT***
2.2 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
Doosan H2017
- **ROBOT MOUNTING**
Fixed Pedestal

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
Not available
- **SAFETY CONFIGURATION** Cobot mode (as an option, safety scanners can be included to increase cycle time)



UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Alu.Profile with covers
- **PALLET DETECTION**
Two photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, PC with screen
- **LIGHT INDICATORS**
Not available
- **MANUAL CONTROL BUTTONS**
Not available
- **CONVEYOR**
Yes included
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price