

MOVECOMPONENTS® 16L - powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
1.3 m x 1.2 m
- **MAX BOX PAYLOAD***
13.5 kg
- **MAX PALLET HEIGHT***
2.4 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
JAKA Pro16
- **ROBOT MOUNTING**
OnRobot Lift100

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION**
CE is included
- **SAFETY CONFIGURATION**
Not included

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Bent sheet metal
- **PALLET DETECTION**
Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, PC with screen
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
Yes, manual pallet confirmation button
- **CONVEYOR****
Available as an option
- **INTERLAYER CONTAINER ****
Available as an option

** The inclusion of additional features may affect the final price