



KNOTTS

D:PLOY Palletizer



TECH SPECIFICATIONS

- **MAX CYCLE TIME*** 9 box/min
- **FOOTPRINT** 62"x72", 62"x119" including pallets
- **MAX BOX PAYLOAD*** Up to 48 lbs
- **MIN/MAX BOX DIMENSIONS** 12"x6"x6" to 24"x12"x10"
- **MAX STACK HEIGHT*** 48"
- **ROBOT MODEL** UR20
- **ROBOT MOUNTING** Fixed pedestal

*Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION** Upon Request
- **SAFETY CONFIGURATION**

Safety scanner included and mounted to front of system.

Two additional safety scanners are recommended and necessary for total area safety coverage

UNIQUE FEATURES

- **BASE MATERIAL** Aluminum Extrusion
- **OPERATOR INTERFACE INCLUDED** Wireless tablet with mounting
- **BASE MATERIAL** Aluminum Extrusion
- **LIGHT INDICATORS** Robot base lighting
- **PALLET ARRANGEMENT** Dual Side
- **PALLET DETECTION** Proximity sensors
- **CONVEYOR** available as an option

** The inclusion of additional features may affect the final price