



# PROPAL20

- powered by D:PLOY

## TECH SPECIFICATIONS

- **MAX CYCLE TIME\***  
10 box/min
- **FOOTPRINT**  
3 m x 1 m
- **MAX BOX PAYLOAD\***  
12 kg
- **MAX PALLET HEIGHT\***  
1.6 m
- **FLEXIBLE PALLET SIZES**  
Yes
- **ROBOT MODEL**  
Jaka Zu20
- **ROBOT MOUNTING**  
Fixed Pedestal

\* Actual performance may differ depending on setup and other environmental factors

## SAFETY

- **SAFETY CERTIFICATION**  
Not included
- **SAFETY CONFIGURATION**  
Cobot mode (as an option, safety scanners can be included to increase cycle time)

## UNIQUE FEATURES

- **PALLET ARRANGEMENT**  
Dual side
- **BASE MATERIAL**  
Stainless steel
- **PALLET DETECTION**  
Two photoelectric sensors
- **OPERATOR INTERFACE INCLUDED**  
Yes, tablet
- **LIGHT INDICATORS**  
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**  
Yes, start/stop button, program selection buttons
- **CONVEYOR\*\***  
Available as an option
- **INERLAYER CONTAINER\*\***  
Available as an option

\*\* The inclusion of additional features may affect the final price