



KEY FEATURES

- ✓ Multi axis force measurement
- ✓ High resolution
- ✓ Highly adaptable product design
- ✓ Dust and water proof (IP65)
- ✓ High overload range
- ✓ Mechanical shock resistant


TECHNICAL SPECIFICATIONS

Sensor Type	3 Axis Force Sensor		Units
Dimensions (H x W x L)	17 x 25 x 25		[mm]
Weight with 1m cable (without)	23 (11)		[g]
	Fz Compression	Fxy	
Nominal capacity (N.C.)	100	± 25	[N]
Typical deformation	3	± 2.5	[mm]
Single axis overload	200 %	200 %	-
Full scale nonlinearity	2 %	2 %	-
Resolution	2.5	2	[mN]
Single axis deformation at N.C.	3	± 2.5	[mm]
Crosstalk (typical)	< 5 %	-	-
Hysteresis (measured on Fz axis, typical)	< 2 %	-	-
Working temperature range	- 40 / +80		[°C]
Power requirement	0.24		[w]

The semi-spherical sensors are only calibrated in z+ direction
 Parameters were measured at room temperature

MECHANICAL DIMENSIONS

INTERFACE TYPES

USB	CAN	UART
Maximum sampling frequency 1000 Hz		
Supported systems Windows and Linux		