

INOPAL - powered by D:PLOY


TECH SPECIFICATIONS

- **MAX CYCLE TIME***
6 box/min in collaborative mode
10 box/min in high speed mode
- **FOOTPRINT** 2.5 m x 1.4 m
- **MAX BOX PAYLOAD*** 27 kg
- **MAX PALLET HEIGHT*** 2.2 m
- **FLEXIBLE PALLET SIZES** Yes
- **ROBOT MODEL** Doosan P3020
- **ROBOT MOUNTING** Fixed pedestal

• Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION** CE is included
- **SAFETY CONFIGURATION**
Robot running in cobot mode (as an option, external safety elements can be included to increase cycle time)



UNIQUE FEATURES

- **PALLET ARRANGEMENT** Two sides
- **BASE MATERIAL** Bent and weld sheet metal
- **PALLET DETECTION** Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, a tablet is included
- **LIGHT INDICATORS** Yes, application status indicator
- **MANUAL CONTROL BUTTONS** Yes (manual pallet confirmation button)
- **CONVEYOR**
Yes, conveyor is included
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price