

StackMate - powered by D:PLOY



TECH SPECIFICATIONS

- **MAX CYCLE TIME***
10 box/min
- **FOOTPRINT**
2.5 x 1.3 m
- **MAX BOX PAYLOAD***
17 kg
- **MAX PALLET HEIGHT***
2.1 m
- **FLEXIBLE PALLET SIZES**
Yes
- **ROBOT MODEL**
Schneider Electric 20 kg cobot
- **ROBOT MOUNTING**
Fixed pedestal

* Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION** Yes (CE)
- **SAFETY CONFIGURATION** Cobot mode (as an option, external safety elements can be included to increase cycle time)

UNIQUE FEATURES

- **PALLET ARRANGEMENT**
Dual side
- **BASE MATERIAL**
Bent and weld sheet metal
- **PALLET DETECTION**
Photoelectric sensor
- **OPERATOR INTERFACE INCLUDED**
Yes, an HMI is included
- **LIGHT INDICATORS**
Yes, application status indicator
- **MANUAL CONTROL BUTTONS**
Yes, pallet confirmation button
- **CONVEYOR**** Available as an option
- **INTERLAYER CONTAINER****
Available as an option

** The inclusion of additional features may affect the final price