



Telabotics CNCTend - POWERED BY D:PLOY



TECH SPECIFICATIONS

- **MAX WORKPIECE WEIGHT**
up to 7 Kg
- **WORKPIECE DIMENSIONS**
Different dimensions can be used, as the grid can be easily reconfigured.
- **NUMBER OF WORKPIECES CAPACITY**
Up to 100 workpieces (capacity dependent on part size)
- **COMMUNICATION TO THE CNC MACHINE**
Ready for HAAS machines.
Compatible with other brands.
- **SINGLE OR DUAL GRIPPER**
Single
- **SOLUTION FOOTPRINT**
48 x 34 "
- **ROBOT MODEL**
TM12X

DIFFERENTIATION ELEMENTS ON THE BASE SOLUTION

- **BASE MATERIAL**
Aluminium profile base
- **TYPE OF GRID FOR WORKPIECES**
Reconfigurable grid suitable for various workpiece geometries.
- **OPERATOR INTERFACE INCLUDED**
Yes, a screen included to operate the system
- **LIGHT INDICATORS**
Available as an option
- **MANUAL CONTROL BUTTONS**
Available as an option
- **CLEANING BLOWER INCLUDED**
Available as an option
- **CNC DOOR OPENER**
Available as an option

SAFETY

- **SAFETY CERTIFICATION**
Risk Assessment Included
- **SAFETY CONFIGURATION**
One area scanner is included