

WET Standard- powered by D:PLOY

TECH SPECIFICATIONS

- **MAX CYCLE TIME***
Up to 6 box/min
- **FOOTPRINT** 3 x 1.4 m
- **MAX BOX PAYLOAD*** 10 kg
(20 kg available with other options)
- **MAX PALLET HEIGHT*** 2.0 m
- **FLEXIBLE PALLET SIZES** Yes
- **ROBOT MODEL** UR20
- **ROBOT MOUNTING** Fixed pedestal

*Actual performance may differ depending on setup and other environmental factors

SAFETY

- **SAFETY CERTIFICATION** CE is included
- **SAFETY CONFIGURATION**
1 Laser Scanner 270° is included



UNIQUE FEATURES

- **PALLET ARRANGEMENT** Two sides
- **BASE MATERIAL** Lacquered steel
- **PALLET DETECTION** Photoelectric sensor on each side
- **OPERATOR INTERFACE INCLUDED** Yes
- **LIGHT INDICATORS** No (available as an option)
- **MANUAL CONTROL BUTTONS** No
- **CONVEYOR** No (available as an option)
- **INTERLAYER CONTAINER**** No (available as an option)

** The inclusion of additional features may affect the final price